


Plano Model Products - #14930 GP30 Cab Sub-Base Step Set Proto2000 Models

The prototypical sized cab sub-base steps in this kit are designed to be used in conjunction with Cannon and Co #2026 GP30 Side Step Set on a Proto2000 GP30 model. They can be added to an undecorated or predecorated model. Extra care will be needed on a predecorated model as the model will need to be disassembled and some modifications will be made to painted features. Please read through these instructions to familiarize yourself with what is about to be required to add these sub-base steps.

Remove the cab from the sill frame and remove the plastic cab step from the right rear cab wall. For the new rear cab step there is a drill template to aid in getting the mounting holes correctly positioned. This template folds up to fit over (around) the lower portion of the right rear cab door wall. At the half etched score lines, bend each section 90 degrees, forming a U shape. Slide this up, centered over the bottom of the wall and drill #78 holes in each hole on the template. The angled shaped step is used in this location and can be added now or later depending on your project. If adding before reinstalling the cab, use extreme caution so you don't damage the step as it is a precise fit. In either case, before adding the step to these drilled holes, carefully bend the front lip down 90 degrees at the half etched score line. When ready, insert mounting pins in drilled holes and CA cement in place.



The plastic front left battery box step will need to be removed, leaving a clean/smooth surface for the new step. Using the other included template, bend 90 degrees at etched line, lay on battery box with holes of template on front surface

of sub base and drill #78 holes in each template hole. Remove step from fret, bend front lip down 90 degrees, insert mounting pins in drilled holes and CA in place.

This completes this portion of your GP30 detailing project. Continue with the rest of your detailing. Here is a list of other GP30 details we have available for your GP30.

- #14805 GP30 Highhood Bell Brackets (2) w/template-Brass
- #14806 GP30 Dynamic Brake Extended Range Cable Cover Box (2) Brass
- #14807 GP30 Dynamic Brake Fan Hatch Plate (2) - Brass
- #14808 GP30 Non-Dynamic Brake Hatch and Fan Blank Plate
- #14809 GP30 Dynamic Brake Extended Range Inspection door - Early Low Hinge - Brass
- #14810 GP30 Dynamic Brake Extended Range Inspection door - Late High Hinge - Brass

Thank you for using our product on your GP30 detailing project. Please see your local hobby dealer for all of our photo etched details. Or visit us online.

Parts as packaged, showing from back side. Trim parts from fret as needed. The fret is the shaded area shown and is discarded when empty.

